



Global Product Portfolio

Healthcare Dispensing Systems





The right dispensing systems partner for your needs

The pharmaceutical industry is as dynamic as ever. With accelerating consolidation, new regulations and shifting priorities, it seems the only constant is change. Operating in this environment can be challenging, particularly as resources are cut but growth expectations remain. Whether you're launching a new product, creating a line extension or seeking an alternative supplier, the right dispensing systems partner can fill the resource gaps and pave the way for growth.

End-to-End Services

Silgan Dispensing Systems Healthcare is more than a supplier of pumps and sprayers for your nasal and topical medications. We provide real value by partnering with you to understand your needs and guide your project through every step of the process. Our global team of experts delivers end-to-end services including consumer insights, design, regulatory affairs, engineering, project management and lab support.

Responsive Manufacturing

When your product demand increases, Silgan Dispensing Systems will be ready. We aim to maintain short lead times and invest in increasing our capacity as the market demands it. We know that capitalising on opportunities as they arise and ensuring supply security are important to you, and we are flexible in our approach to providing you with a level of service that exceeds your expectations and helps you deliver results.

Industry-Leading Solutions

We believe that packaging does more than simply contain or dispense medication. Well-thought-out quality packaging can give your brand an edge in the marketplace that translates to improved patient loyalty, satisfaction and adherence. At Silgan Dispensing Systems, we infuse consumer insights throughout our development process to provide your patients with superior healthcare dispensing systems.

Pump Solutions



MK™

Key Features

- Outstanding performance and dose accuracy
- Accurate priming for OTC or Rx formulations
- All pharma-grade materials comply with European and U.S. regulations
- Compliant with the U.S. FDA nasal guidelines
- Has a Drug Master File (DMF)
- Standard white colour; other colours available upon request
- Available with shipping clip for various sizes and outputs
- Available with protective hood for nasal adapters in custom colours

Closure Sizes

Many standard closure sizes

Output Range

0.050 to 0.180 ml



Mark II™

Key Features

- Excellent atomisation capabilities with great performance and quality
- Has a Drug Master File (DMF)
- All pharma-grade materials comply with European and U.S. regulations
- Standard white colour; other colours available upon request
- Available with shipping clip for various sizes and outputs
- Available with protective hood for nasal adapters in custom colours

Closure Sizes

Many standard closure sizes

Output Range

0.100 to 0.200 ml



Mark VII® Max

Key Features

- Compatible with most high-viscosity formulations
- Spray and cream versions with excellent priming and smooth actuation
- Natural gasket for invisibility in translucent closures
- Variety of closures, heads, hoods and orifice cups for maximum flexibility and compatibility across platforms and product lines
- Inverted version available for upside-down spraying

Closure Sizes

Ribbed: GL 20, 20-400
Smooth or ribbed: 20-410, 22-415, 24-410
Snap-on: GS 30, GS 31
Ferrule: 20 mm

Outputs

0.160, 0.210, 0.300 ml
0.180 ml for inverted version



SD 200®

Key Features

- Intermediate output
- Advanced lock-down design
- Outstanding top-load support
- Wide variety of head designs
- Range of options for packaging convenience and flexibility

Closure Sizes

Ribbed: 24-400
Smooth or ribbed: 24-410, 24-415, 28-410, 28-415

Outputs

2.0 ml



Sprayette™ IV

Key Features

- Pure Path™ technology for a metal-free fluid pathway
- Highly customisable with variety of output sizes and protective hoods
- Higher-output large mist sprayer
- Exceptional performance with aggressive formulas
- Wide range of spray pattern options
- High discharge volume for oral and topical applications

Closure Sizes

24-410, 28-400, Snap-on S26

Output Range

0.350 to 0.700 ml



HiMark®

Key Features

- Versatile product range with many options for outputs, closures and adapters
- Easily customised with numerous aesthetic options
- Topical, oral and nasal options available
- Dose counter and safety clip options available
- Suitable for non-drip nasal sprays and other viscous formulations
- Wide output range with many options
- For aggressive products, alternative materials can be provided for critical pump components
- Child-resistant option available

Closure Sizes

Many standard closure sizes

Output Range

0.050 to 0.190 ml



HiMark® CR

Key Features

- Meets highest level of child resistance while still being easy for adults to use
- Integrated locking feature provides security, even if the hood is lost or left off
- One of our most versatile pump engines, it is suitable for a range of difficult, viscous and aggressive formulations
- Available in a wide range of dimensions, finishes, spray angles and outputs
- Backed by a Drug Master File (DMF)

Closure Sizes

GPI 18 – 415 non-removable

Outputs

0.050, 0.100 ml

Preservative-Free Solutions



PFP N™ (Nasal)

Key Features

- Full protection from microbiological contamination
- No silver spring, no oligodynamic components
- Shut-off valve to avoid contamination
- Sterile air filter system for bottle venting; non-venting version also available
- Entire pump can be sterilised via gamma irradiation
- Has a Drug Master File (DMF)
- Finger flange and hood can be easily customised
- Standard white colour, with clear and custom colours available
- All pharma-grade materials comply with European and U.S. regulations
- Extensive reference list

Closure Sizes

Snap-on closure S20

Output Range

0.050 to 0.140 ml with customised intermediary outputs

Eye Dropper Solutions



Iridya™

Key Features

- Preservative-free, multidose eye dropper
- Familiar squeeze-bottle dropper design
- Consumer-preferred design validated by qualitative testing
- Elongated tip for ease of use and precision
- Tamper-evident tear-off strip
- Overcap for prolonged use and on-the-go lifestyles
- Low squeeze force
- Controlled application for exact dosing
- Compatible with most market formulations, from low to high viscosities
- Delivery system for both over-the-counter and prescription drugs



Bottle Sizes and Makes

- 10 ml (standard), other sizes upon request
- White and transparent bottles available
- Senior-friendly soft material for low bottle squeeze force

Color Options

Diverse hood/overcap colours available

Outputs

25–45 µl, depending on formulation
Custom outputs available



Adapters

Nasal Applications



Round



Square



Oval



Mini



Ear Adapter



Shroud 20²



Hexagon



Dose Counter¹



Elegant

Oral Applications



Throat Adapter
Short



Throat Adapter
Medium



Throat Adapter
Medium + Protection



MTA5¹




Spray Extender²



Throat Adapter Long



Throat Adapter Long
with Wings



Throat Adapter Articulated³



ATA 19



SATA Narrow

Topical Applications



Dispensing Head



Spray Head 16 mm



Spray Head with Capillary Tube⁴



Spray Head 16 mm

Ophthalmic Applications

All adapters fit on Mark II and MK with the below exceptions:

¹ Dose counter and MTA5 fit on HiMark

² Spray extender fits on Mark VII Max

³ Throat adapter articulated-F on ferrule only

⁴ Spray head on capillary tube on special request only

Additional nasal, oral, topical and ear adapters available through partners

OFFICES

North America

Silgan Dispensing Headquarters
1001 Haxall Point, Suite 701
Richmond, VA 23219 USA
Phone: +1 (804) 444-1000

Silgan Dispensing Office
845 3rd Avenue, Suite 623
New York, NY 10022 USA
Phone: +1 (646) 290-5205

Silgan Dispensing Systems Canada Ltd.
7381 Bramalea Road
Mississauga, ON Canada L5S 1S4
Phone: +1 (905) 364-2675
Fax: +1 (905) 364-2679

Europe

Silgan Dispensing Systems France S.A.S
(not a selling entity)
Le Campus
Bât B-Est
Rue Jean-Pierre Timbaud
78180 Montigny le Bretonneux France
Phone: +33 1 39 48 12 70

Silgan Dispensing Systems Netherlands B.V. (not a selling entity)
16 Professor Asserweg
Waalwijk, NB 5144 NC
North Brabant, Netherlands
Phone: +31 (0) 416321602

Asia

Shanghai Office
Room 802, Nan Yang 1931 Building,
No. 165 Yu De Road
Shanghai 200030
Phone: +86 21 6029 3681

Silgan Dispensing Systems India Private Limited
Office #434, Regus, 4th Floor,
Gumidelli Towers
Old Airport Road, Begumpet
Hyderabad 500016 Telangana India
Phone: +91 7675803666 or
+91 9619884663

PLANTS

North America

Spring Plant in
Washington Court House, OH
238 South Main Street
Washington Court House, OH 43160 USA
Phone: +1 (740) 335-8400

Silgan Dispensing Systems Corporation
11901 Grandview Road
Grandview, MO 64030 USA
Phone: +1 (816) 986-6000

Silgan Dispensing Systems Slatersville LLC
110 Graham Drive
North Smithfield, RI 02876 USA
Phone: +1 (401) 767-2400

Silgan Dispensing Systems Corporation
3719 East 12th Avenue
Winfield, KS 67156 USA
Phone: +1 (620) 229-5000

Silgan Dispensing Systems Mexico S.A. de C.V.
Circuito Exportaciones 371
Parque Industrial Tres Naciones
San Luis Potosí, S.L.P. 78395 Mexico
Phone: +011 52 444 870 1100

Silgan Dispensing Systems Mexico Operadora
Boulevard Insurgentes No. 18895-3
Cerro Colorado
Tijuana, B.C. 22590 Mexico
Phone: +011 52 664 6268305

South America

Silgan Dispensing Systems Brazil Packaging Industry Ltda.
Estrada Municipal Governador Mário
Covas, 600
Valinhos, S.P., 13279-411, Brazil
Phone: +55 19 3881 8803

Europe

Silgan Dispensing Systems Barcelona SL
Via Trajana, 25
Barcelona, 08020 Spain
Phone: +34 93 314 9111

Silgan Dispensing Systems Hemer GmbH
Ernst – Stenner – Straße 17
58675 Hemer Germany
Phone: +49 23 72 5040

Silgan Dispensing Systems Milano S.r.l.
Strada Statale 35 dei Giovi, 1/B
20080 Zibido San Giacomo, MI Italy
Phone: +39 02 90 41 461

Silgan Dispensing Systems Vicenza S.r.l.
Via Monte Tomba 28a
36060 Romano d' Ezzelino, (VI) Italy
Phone: +39 0424 839111

Asia

Silgan Dispensing Systems Co. Ltd.
19 Xindu Road Wuxi-Singapore
Industrial Park
Wuxi, 214028 PR China
Phone: +86 510 8528 2008